


Floor scale KERN BFB



Weighing bridge with screwed-on weighing plate (IP67) and XXL display device, with EC type approval [M]



Weighing plate can be unscrewed
The weighing plate can be conveniently
unscrewed for maintenance or cleaning
purposes (weighing plate size ,)




Easy levelling of the weighing bridge as well as access to the junction box from above



Did you know? Our floor scales are delivered in a robust wooden box. This protects the high-quality weighing technology from environmental influences and stresses during transportation. KERN – always one step ahead







Features

- · Weighing plate A, B screwed on from the top, so it's easy to remove, hygienic and easy to clean
- II Weighing bridge: steel, painted, weighing plate size , D corrugated steel plate, welded, 4 silicone-coated steel load cells, dust and spray protection IP67
- · Display device: for details see KERN KFB-TM
- · Benchtop stand incl. wall mount for display device as standard
- Totalising of weights and piece counts
- Protective working cover included with delivery

Technical data

- · Large backlit LCD display, digit height 52 mm
- · Weighing plate dimensions W×D×H
- A 1000×1000×85 mm
- **■** 1500×1250×85 mm
- I 1500×1500×80 mm
- D 1500×1500×130 mm
- Dimensions of display device W×D×H 250×160×58 mm
- Cable length of display device approx. 5 m
- Permissible ambient temperature -10 °C/40 °C

Accessories

- · Protective working cover, scope of delivery: 5 items, KERN KFB-A02S05
- 2 Stand to elevate display device, height of stand approx. 800 mm, KERN BFS-A07
- · Pair of base plates to fix the weighing bridge to the floor, for models with weighing plate size
 - A, B, C KERN BFS-A06N
 - KERN BFS-A10
- 3 Ascending ramp, steel, lacquered, not included, for models with weighing plate size
 - A KERN BFS-A01N
 - **B** KERN BFS-A02N
- **©** KERN BFS-A09N
- **D** KERN BFS-A11
- 4 Stable pit frame, steel, lacquered, for models with weighing plate size
 - A KERN BFS-A03N
 - **B** KERN BFS-A04N
- **©** KERN BFS-A08
- · Rechargeable battery pack internal, operating time up to 35 h without backlight, charging time approx. 10 h, must be ordered at purchase, KERN KFB-A01

- · Bluetooth data interface for wireless data transfer to PC or tablets, must be ordered at purchase, not in combination with verification, not possible in combination with RS-232 data interface, KERN KFB-A03
- · Analogue module, must be ordered at purchase, not possible in combination with signal lamp
- 0-10 V: KERN KFB-A04
- 4-20 mA: KERN KFB-A05
- Signal lamp for visual support of weighing with tolerance range, KERN CFS-A03
- · Large display with superior display size, KERN YKD-A02
- Cable with special length 15 m, between display device and platform, for verified models which must be ordered at the time of purchase, KERN BFB-A03
- · Further details, plenty of further accessories and suitable printers see Accessories

Note: For verified scales the weighing bridge must be fixed to the floor. Optionally, with an access ramp, a footplate pair or a pit frame

Shipment via freight forwarder. Please ask for dimensions, gross weight, shipping costs







































Model	Weighing	Readability	Minimal load	Net weight	Weighing plate	Option			
	capacity	= Verification value				Verification		DAkkS Calibr. Certificate	
	[Max]	[d] = [e]	[Min]	approx.		MIII		DAkkS	
KERN	kg	kg	kg	kg		KERN		KERN	
BFB 600K-1SNM	600	0,2	4	105	Α	965-230		963-130	
BFB 600K-1NM	600	0,2	4	135	В	965-230		963-130	
BFB 1T-4SNM	1500	0,5	10	100	Α	965-230		963-130	
BFB 1T-4NM	1500	0,5	10	135	В	965-230		963-130	
BFB 3T-3NM	3000	1	20	135	В	965-232		963-132	
BFB 3T1LM	3000	1	20	155	С	965-232		963-132	
BFB 6T-3M	6000	2	40	210	D	965-232		963-132	

Note: For applications that require verification, please order verification at the same time, initial verification at a later date is not possible. Verification at the factory, we need to know the full address of the location of use.

Pictograms



Internal adjusting:

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required



Easy Touch:

Suitable for the connection, data transmission and control through PC, tablet or smartphone



Memory:

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



Alibi memory:

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.



Data interface RS-232:

To connect the balance to a printer, PC or network



RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



USB data interface:

To connect the balance to a printer, PC or other peripherals



Bluetooth* data interface:

To transfer data from the balance to a printer, PC or other peripherals



WLAN data interface:

To transfer data from the balance to a printer, PC or other peripherals



Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



Analogue interface:

to connect a suitable peripheral device for analogue processing of the measurements



Interface for second balance:

For direct connection of a second balance




Network interface:

For connecting the scale to an Ethernet network



Wireless data transfer:

between the weighing unit and the evaluation unit using an integrated radio module





KERN Communication Protocol (KCP):

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO log:

The balance displays serial number, user ID, weight, date and time, regardless of a printer connection



GLP/ISO log:

With weight, date and time. Only with KERN printers



Piece counting:

Reference quantities selectable. Display can be switched from piece to weight



Recipe level A:

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



Recipe level B:

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display



Recipe level C:

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display, multiplier function, adjustment of recipe when dosages are exceeded or barcode recognition



Totalising level A:

The weights of similar items can be added together and the total can be printed out



Percentage determination:

Determining the deviation in % from the target value (100 %)



Weighing units:

Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details



Weighing with tolerance range:

(Checkweighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



MOVE

Hold function:

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram.



Stainless steel:

The balance is protected against corrosion



Suspended weighing:

Load support with hook on the underside of the halance



Battery operation:

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack:

Rechargeable set



Universal mains adapter:

with universal input and optional input socket adapters for A) EU, CH, GB; B) EU, CH, GB, USA; C) EU, CH, GB, USA, AUS



Mains adapter:

230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available



Power supply:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



Weighing principle: Strain gauges

Electrical resistor on an elastic deforming body



Weighing principle: Tuning fork

A resonating body is electromagnetically excited, causing it to oscillate



Weighing principle: Electromagnetic force compensation

Coil inside a permanent magnet. For the most accurate weighings



Weighing principle: Single cell technology:

Advanced version of the force compensation principle with the highest level of precision



Verification possible:

The time required for verification is specified in the pictogram



DAkkS calibration possible:

The time required for DAkkS calibration is shown in days in the pictogram



Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram

KERN - Precision is our business

To ensure the high precision of your balance KERN offers you the the appropriate test weight in the international OIML error limit classes E1-M3 from 1 mg - 2500 kg. In combination with a DAkkS calibration certificate the best pre-requisite for proper

The KERN DAkkS calibration laboratory today is one of the most modern and bestequipped DAkkS calibration laboratories for balances, test weights and force-measure-

ment in Europe.

Thanks to the high level of automation, we can carry out DAkkS calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

Range of services

- DAkkS calibration of balances with a maximum load of up to 50 t
- DAkkS calibration of weights in the range of 1 mg 2500 kg
- Volume determination and measuring of magnetic susceptibility (magnetic characteristics) for test weights
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DAkkS calibration certificates in the following languages DE, GB, FR, IT, ES, NL, PL
- Conformity evaluation and reverification of balances and test weights

Your KERN specialist dealer:

ICS Schneider Messtechnik GmbH Briesestraße 59 D-16562 Hohen Neuendorf / OT Bergfelde

Tel.: 03303 / 50 40 66 Fax: 03303 / 50 40 68

info@ics-schneider.de www.ics-schneider.de