

## Temperature calibrator TP M255S

TP Solid // Calibration bath // Room temperature...255 °C // RT...491 °F



TP M255S



### Highlights

- Very easy operation with 4-button control and integrated reference temperature sensor
- PC interface with connection cable to USB for use with SIKA calibration software
- Low weight and stable handle for easy transport
- Optional accessory: Transport case with or without trolley
- Qualified for SIKA Gold Service
- Especially suitable for calibration of devices under test with special sensor geometry. DUTs are simply immersed in the calibration liquid, no calibration insert with specific bore hole pattern is required.

### TP Solid

With the temperature calibrators of the TP Solid series, the main focus is on **flexibility**: In addition to **dry block calibrators**, they also include **calibration baths**, with which almost any temperature sensor can be calibrated irrespective of its shape. Both can be operated **easily and intuitively**. When being used as fluid bath calibrator, the temperature sensors are directly immersed into the calibration liquid. This creates a direct temperature link

between the calibrator and the devices under test without insulating air gap. All TP Solid temperature calibrators are additionally equipped with a **serial interface for computer-assisted monitoring** of the calibration process. This flexibility in combination with the easy operation make the TP Solid series ideal for **use in machinery and plant engineering**.

### SIKA temperature calibrators

Temperature calibrators are used for the verification of the functionality and calibration of temperature measuring devices and temperature sensors. As the sole German manufacturer of these devices, we develop and produce our "Made in Germany" temperature calibrators with a special focus on **long-term reliability** and **utmost accuracy** in combination with **easy operation**. We can rely on more than 40 years of experience in doing this: SIKA's **first dry block temperature calibrator** was launched all the way back in 1980.

Every SIKA temperature calibrator is meticulously tested for **accuracy** and **stability**. This is attested by our standard calibration certificate, which we issue with every temperature calibrator, or by means of an optional DAkkS calibration certificate [German accreditation body]. This is to guarantee that you receive a **perfect product** which can be traced back to national and international temperature measurement standards.

# Features

## Easy operation

- The TP M255S can be operated with only four buttons: Two arrow buttons for setting the target temperature, one button for confirmation and one return button
- Thus, temperatures can be set as easily as, for example, in the air conditioning system in your car
- Any operational errors can be nearly excluded. You do not need any specifically trained staff or time-consuming briefings



## TT-Scan multi-channel measuring instrument

- To calibrate devices under test that do not have their own temperature display, you need to connect them to a measuring instrument
- This is done by our TT-Scan multi-channel measuring instrument: With this instrument, you can calibrate up to eight DUTs without a display unit of their own
- The TT-Scan and the temperature calibrator are connected to a PC or laptop on which the temperatures of the DUTs are output via our PC software and evaluated.
- Compatible with DUTs with all common signals: Resistance thermometer, thermocouple and current signals
- The simultaneous calibration of several DUTs enables great time savings

## SIKA Gold Service







SIKA Gold Service provides a comprehensive service package for the regular recalibration of your temperature calibrator. You will benefit from exclusive savings and discounts as well as special promotions reserved to SIKA Gold Service members.

- You will save 33% in the recalibration of your temperature calibrator
- You will receive a 10% discount on any repairs that may become necessary
- You will receive preferential invitations to product presentations, symposia, practice days and exclusive training offers

Register now and benefit from the SIKA Gold Service: [gold-service.sika.net](http://gold-service.sika.net)



## Technical data

TP M255S		
<b>Temperature range</b>	Room temperature...255 °C	Room temperature...491 °F
<b>Calibration volume</b>	Ø 60 x 170 mm	
Calibration bath		
<b>Display accuracy</b>	±0.2 °C	±0.36 °F
<b>Temperature stability</b>	±0.05 °C	±0.09 °F
<b>Resolution of the temperature display</b>	0.01 °C in the range -9.99...99.99 °C, else 0.1 °C	0.01 °F in the range -9.99...99.99 °F, else 0.1 °F
<b>Reference temperature sensor</b>	internal, fixed installation	
<b>Interface</b>	RS485 (calibrator) to USB (PC)	
<b>Connectivity</b>	MODBUS	
Dimensions		
→ Width	150 mm	
→ Height	330 + 70 mm	
→ Depth	270 mm	
<b>Weight</b>	Approx. 7.5 kg	
<b>Power supply</b>	110...115 V 60 Hz / 230 V 50 Hz	
<b>Power consumption</b>	Approx. 1000 W	
Display		
<b>Display</b>	2-line, 4-digit digital display, red / green, unit °C / °F	
Approvals		
     		

# Article numbers

To order a complete calibrator, you need two article numbers:

1. Calibrator
2. Calibration insert

In addition, depending on your individual calibration requirements, you can order additional calibration inserts, necessary certificates and other accessories.

1. Calibrator					
Temperature range	Function	Calibration insert [mm]	Power supply	Article number	
Room temperature...255 °C	RT...491 °F	Calibration bath	Ø 60 x 170	100...230 V	EPMB250S601503

**Notice:** Every "linearisation" article number with 13 digits starts with "EK1", while the following letters ("short designation") indicate the selected calibration function. You may also select several functions of one category. Please indicate the calibration functions in alphabetical order and fill in any possibly remaining positions with "0".

2. Linearisation											
Calibration function	Calibration insert / calibration medium			Reference temperature sensor				Short designation			
Calibration bath (Direct filling)	20 cSt	7...220 °C	44.6...428 °F	internal				R			
	50 cSt	50...270 °C	122...518 °F	internal				T			
Example article number linearisation											
Function:		1	2	3	4	5	6	7	8	9	10
Article number:	EK1	T	0	0	0	0	0	0	0	0	0

3. Calibration certificate - Select your calibration certificates as needed		Article number
Each calibrator is already delivered with a standard calibration certificate (3 test points).		
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 1st calibrator function		EKTPWP1FKT
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 2nd calibrator function		EKTPWP2FKT
DAkKS calibration certificate (3 test points + measurement uncertainty determination) for 1st calibrator function		EKTPDAKKS1FKT
DAkKS calibration certificate (3 test points + measurement uncertainty determination) for 2nd calibrator function		EKTPDAKKS2FKT
Each additional test point DAkKS calibration certificate		EKTPDAKKSZUSP
SIKA Gold Service works calibration certificate		EKTPGOLDWP
SIKA Gold Service DAkKS		EKTPGOLDDAKKS

4. Accessories		Article number
Transport case without trolley		EZTPKOFFER20
Transport case with trolley		EZTPKOFFER20TG
Tripod (holder for devices under test)		EZTPMSG0000000
Calibration liquid (silicone oil), 50cSt		EZSÖ0500000000
PC software (without TT-Scan)		EZ999999999971
PC software (with TT-Scan)		EZ380000000001
PC connection cable: temperature calibrator (RS485) to USB		EZ170000000002

# Overview of SIKA temperature calibrators

## Our series: Basic. Solid. Premium.

- **Dry block calibrators** of the **TP Basic** series impress with their **uncomplicated operation** and **high cost-effectiveness**. They are particularly suitable for use on ships or in industrial applications.
- Equipped with a **PC interface**, the **dry block calibrators** and **calibration baths** of the **TP Solid** series cover a wide temperature range with high accuracy.
- For the highest demands on accuracy and flexibility: The dry-block and multi-function temperature calibrators of the **TP Premium** series represent the pinnacle of our technical development. Equipped with an **integrated touch screen**, a **PC interface**, an **external reference sensor** and **integrated measuring instrument**, this series offers **extreme accuracies** for **all calibration tasks**.

Temperature range (RT=Room temperature)	Function	Accuracy	Features	Block dimensions [Ø mm x depth mm]	Type	
-55 °C ... 200 °C -67 °F ... 392 °F	Dry block	±0.4 °C	±0.72 °F	TP Basic	28 x 150	TP 17200
	Dry block	±0.2 °C	±0.36 °F	TP Solid	28 x 150	TP 17200S
	Dry block	±0.2 °C	±0.36 °F	TP Premium	28 x 150	TP 37200E.2
-35 °C ... 155 °C -31 °F ... 311 °F	Calibration bath	±0.1 °C	±0.18 °F	TP Solid	60 x 170	TP M165S
-35 °C ... 165 °C -31 °F ... 329 °F	Dry block	±1 °C	±1.80 °F	TP Basic	28 x 150	TP 17165M
	Dry block	±0.4 °C	±0.72 °F	TP Basic	28 x 150	TP 17165
	Dry block	±0.2 °C	±0.36 °F	TP Solid	28 x 150	TP 17165S
	Dry block	±0.2 °C	±0.36 °F	TP Premium	28 x 150	TP 37165E.2
	Dry block ext. Dry block int.	±0.2 °C ±0.3 °C	±0.36 °F ±0.54 °F	TP Premium	60 x 170	TP 3M165E.2
	Air Shield Insert	±0.099 °C	±0.1782 °F			
Calibration bath Infrared Surface	±0.1 °C ±0.5 °C ±1 °C	±0.18 °F ±0.9 °F ±1.88 °F				
-30 °C ... 165 °C -22 °F ... 329 °F	Dry block	±0.4 °C	±0.72 °F	TP Basic	60 x 150	TP 17166
	Dry block	±0.2 °C	±0.36 °F	TP Solid	60 x 150	TP 17166S
-10 °C ... 100 °C 14 °F ... 212 °F	Dry block	±0.05 °C	±0.09 °F	TP Solid	7 x 6.5 x 150	TP 17Zero
RT ... 200 °C RT ... 392 °F	Dry block	±1 °C	±1.80 °F	TP Basic	18 x 150	TP 18200E
RT ... 255 °C RT ... 491 °F	Calibration bath	±0.2 °C	±0.36 °F	TP Solid	60 x 170	TP M255S
	Dry block ext. Dry block int.	±0.25 °C ±0.5 °C	±0.45 °F ±0.9 °F	TP Premium	60 x 170	TP 3M255E.2
	Air Shield Insert	±0.08 °C	±0.144 °F			
	Calibration bath, tub insert, ext.	±0.35 °C	±0.63 °F			
	Calibration bath, tub insert, int.	±0.53 °C	±0.954 °F			
	Calibration bath, direct filling, ext.	±0.18 °C	±0.324 °F			
	Calibration bath, direct filling, int.	±0.46 °C	±0.828 °F			
Infrared Surface	±0.5 °C ±1 °C	±0.9 °F ±1.8 °F				
RT ... 450 °C RT ... 842 °F	Dry block	±0.6 °C	±1.08 °F	TP Basic	60 x 150	TP 17450
	Dry block	±0.3 °C	±0.54 °F	TP Solid	60 x 150	TP 17450S
	Dry block Air Shield Insert	±0.3 °C ±0.2 °C	±0.54 °F ±0.36 °F	TP Premium	60 x 150	TP 37450E.2
	Infrared Surface	±0.5 °C ±1 °C	±0.9 °F ±1.8 °F			
RT ... 650 °C RT ... 1202 °F	Dry block	±1 °C	±1.8 °F	TP Basic	28 x 150	TP 17650M
	Dry block	±0.8 °C	±1.44 °F	TP Basic	28 x 150	TP 17650
	Dry block	±0.4 °C	±0.72 °F	TP Solid	28 x 150	TP 17650S
RT ... 700 °C RT ... 1292 °F	Dry block Air Shield Insert	±0.43 °C ±0.27 °C	±0.744 °F ±0.486 °F	TP Premium	29 x 150	TP 37700E.2
RT ... 850 °C RT ... 1562 °F	Dry block	±1 °C	±1.8 °F	TP Basic	18 x 100	TP 18850E
400 °C ... 1300 °C 752 °F ... 2372 °F	Dry block	±2 °C	±3.6 °F	TP Solid	28 x 200	TP 281300E