

# Portable SF<sub>6</sub> transfer unit Model GTU-10

# EAC

## **Applications**

- Pumping SF<sub>6</sub> gas out of equipment into gas cylinders
- Consolidating part-filled SF<sub>6</sub> gas cylinders
- Filling of SF<sub>6</sub> gas-insulated equipment

## Special features

- High compressor performance
- Compact dimensions
- Robust version for the service
- Clear display of the working pressure



Portable SF<sub>6</sub> transfer unit, model GTU-10

### Description

#### Portable service equipment series

The model GTU-10 SF<sub>6</sub> transfer unit is a module of the portable service equipment series.

Modules of the series:

- Portable vacuum pump, model GVP-10
- Portable SF<sub>6</sub> filter unit, model GPF-10
- Portable SF<sub>6</sub> vacuum compressor, model GVC-10
- Portable SF<sub>6</sub> transfer unit, model GTU-10
- Portable SF<sub>6</sub> gas cylinder scale, model GWS-10

The model GTU-10 is an instrument developed specifically for  $SF_6$  gas. Due to the selection of the oil-free running compressors, contamination of the  $SF_6$  gas by lubricant is eliminated.

The compact dimensions of the model GTU-10 are ideal for mobile use. The fields of application range from the storage of  $SF_6$  gas in gas tanks to the filling of  $SF_6$  gas-insulated switches.

During storage of the  $SF_6$  gas, the compressor can liquefy the gas in the storage vessel. Thus, the maximum storage capacity of a gas cylinder can be used. The connected storage vessels and supply lines must therefore be designed and approved for at least 50 bar pressure.


Tel.: 03303 / 504066

Fax: 03303 / 504068

# **Functionality**

The compressor is connected to the input and output sides with appropriate fittings and hoses.

After switching on the compressor, the  $SF_6$  gas is transported from the input to the output. With rising filling pressure, the  $SF_6$  gas is liquefied in the storage vessel with minimum space requirements. The compressor automatically switches off when reaching 40 bar abs., and the overpressure warning



lamp illuminates.

Switching on again is only possible once the pressure at the output has dropped below 36 bar abs.

Depending on the selection of the output valve ( 10 = output not pressure-reduced, 9 = output pressure-reduced) the gas drawn in is pumped into the connected vessel via the output hose. The desired filling pressure can thus be set exactly at the built-in pressure reducer.

- Overpressure warning lamp
- 2 On/Off switch
- 3 Pressure display, inlet pressure
- 4 Operating hours counter
- 5 Pressure reducer
- 6 Pressure display, output pressure reducer
- 7 Pressure display output pressure
- 8 Valve coupling, inlet, DN 8
- 9 Valve coupling, outlet pressure reducer, DN 8
- Valve coupling, outlet, DN 8

# **Specifications**

#### Gas flow rate

1.1 m<sup>3</sup>/h

#### Permissible inlet and outlet pressure

≤ 40 bar abs. [580 psia]

#### Pressure reducer, outlet pressure

0 ... 16 bar [0 ... 232 psig]

#### **Power supply**

Available versions	
Standard	AC 230 V, 50 Hz, ±10 %
Option	AC 115 V, 60 Hz, ±10 %

#### Permissible ambient temperature

Storage: -20 ... +60 °C [-4 ... +140 °F] Operation: 5 ... 40 °C [41 ... 104 °F]

### Permissible humidity

≤ 90 % r. h. (non-condensing)

#### Ingress protection

IP20 (per IEC 60529)

#### Weight


Approx. 30 kg [66 lbs]

# **Approvals**

Logo	Description	Country
C€	EU declaration of conformity  ■ EMC directive EN 61326 emission (group 1, class B) and interference immunity (industrial application) ■ Machinery directive ■ RoHS directive	European Union
ERC	EAC ■ EMC directive ■ Low voltage directive ■ Machinery directive	Eurasian Economic Community

Approvals and certificates, see website

# Dimensions in mm [inch]



# **Accessories**

# **Connecting hoses**

Designation	Order number			
	Stainless steel	Rubber		
Hose with self-sealing valves, DN 8				
Length 3 m [9.8 ft]	14225424	14064928		
Length 6 m [19.7 ft]	14225507	14064929		
Length 12 m [39.4 ft]	14225513	14064931		
Length 15 m [49.2 ft]	14225522	14064933		

# Adapter

Designation	Order number		
Adapter for GA45 gas recovery bag			
DN8 to quick connector	14068883		
Adapter for gas cylinder			
DN8 to W21.8 x 1/14" per DIN 477 No. 6	14074524		
DN8 to 0.96" 15/16" CGA 590	14074523		
DN8 to 1" per DIN 477 No. 8	14074521		
DN8 to G 5/8" per BS 341 No. 6	14074525		

# Gas recovery bag

Designation	Order number
Gas recovery bag, model GA45	14013015
For specifications see data sheet SP 62.08	

Tel.: 03303 / 504066

Fax: 03303 / 504068