



MULTISCAN ++MED

MED-approved SIL2 Control Panel

Marine, ATEX and SIL2 certified Up to 2 closed RS485 (EIA-485) galvanic isolated loops Up to 64 inputs

ICS Schneider Messtechnik GmbH Briesestraße 59 D-16562 Hohen Neuendorf / OT Bergfelde

Tel.: 03303 / 50 40 66 Fax.: 03303 / 50 40 68

FORBIDDEN TO OPEN to unauthorised

> info@ics-schneider.de www.ics-schneider.de

Specification

Size	500 x W500 x D220 mm (19.69 x 19.69 x 8.66ins)
Power	230 Vac box version
Operating temperature	0 - +55°C
Humidity	15 - 85%
Inputs	Max. 64 RS485 communication gas detectors loop connected (IDI version) or 4- 20 mA through STG/IN8-S modules
Outputs	8 relays onboard the panel. 128 open collectors on remote modules STG/OUT16-S2 . 8-relay board to connect to STG/OUT16-S2 modules
Communication Port	RS485 Modbus communication
Event logging	The event log can be visualised from the gas panel or by the software
Panel indication	Graphic Liquid Crystal Display (LCD)
Approvals	EMC, ATEX
Functional Safety	SIL2

Tel.: 03303 / 50 40 66 Fax.: 03303 / 50 40 68